Eyesaver® Classic Laboratory Faucet with Integrated Eyewash

# **EYEWASH FEATURES:**

- Independent water channel for eyewash
- Brass spindle valve
- Pull handle activation
- Aerated yellow plastic spray outlets with integral flow control and flip-top dust caps
- 2.43 GPM (9.2 L/min) @ 30 PSI flow rate
- 1/2" NPT male inlet

## **FAUCET FEATURES:**

- Brass construction with polished chrome finish
- Gooseneck spout with independent water channel for faucet
- 2.2 GPM (8.3 L/min) flow rate
- Inlet supply 3/8" compression with female threads

# **EYEWASH OPTIONS:**

• NA: Non-aerated eyewash outlets

# **FAUCET OPTIONS:**

- 8: 8" Gooseneck spout for faucet
- BO: 0.5 GPM (1.89 L/min) faucet flow control
- FP: foot pedal for faucet operation (Not NSF 61/372 compliant)
- LF: 1.5 GPM (5.7 L/min) laminar faucet flow control
- ST: Serrated tip for faucet with vacuum breaker (Not NSF 61/372 compliant)
- TW: Thermostatic mixing valve for tepid water during eyewash usage

#### **STANDARDS:**

- ANSI/ISEA Z358.1 certified
- ASME A112.18.1/CSA B125.1 certified
- IGC 272 certified
- NSF/ANSI 61 certified
- NSF 372 certified

## **WARRANTY:**

Visit www.speakman.com for full product warranty information

• 3 Year Limited Warranty (commercial)





Information continues on next page


## **ENSURE YOU ARE ANSI/ISEA Z358.1 Tepid Water Compliant** by incorporating Speakman's 9.7 GPM Thermostatic Mixing Valve.




- -TW OPTION: Add the -TW suffix to the part number, this product ships complete with the TMV and connections
- STW-370: Thermostatic Mixing Valve (valve only)
- SEF-TW: Thermostatic Mixing Valve with necessary connections for SEF products

All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice

# Eyesaver® Classic Laboratory Faucet with Integrated Eyewash





SEF-1000-CA Spray Plume Length and Flow										
Flowing Pressure	30 psi	40 psi	50 psi	60 psi	70 psi	80 psi				
	2.07 Bar	2.76 Bar	3.45 Bar	4.14 Bar	4.83 Bar	5.52 Bar				
Flow Rate	2.9 gpm	3.1 gpm	2.9 gpm	2.9 gpm	2.9 gpm	2.9 gpm				
Flow Rate	11.09 L/min	11.55 L/min	11.13 L/min	10.98 L/min	10.90 L/min	10.86 L/min				
Eyewash Distance	13.5"	14.25"	14.25"	13.75"	13.75"	13.75"				
Plume "A"	34.29 cm	36.2 cm	36.2 cm	34.93 cm	34.93 cm	34.93 cm				

	SEF-1000-CA-8 Spray Plume Length and Flow										
Flow	Flowing Pressure	30 psi	40 psi	50 psi	60 psi	70 psi	80 psi				
		2.07 Bar	2.76 Bar	3.45 Bar	4.14 Bar	4.83 Bar	5.52 Bar				
	Flow Rate	2.9 gpm	3.1 gpm	2.9 gpm	2.9 gpm	2.9 gpm	2.9 gpm				
		11.09 L/min	11.55 L/min	11.13 L/min	10.98 L/min	10.90 L/min	10.86 L/min				
	Eyewash Distance	17.0"	18"	17.5"	17.0"	17.0"	17.0"				
	Plume "A"	43.18 cm	45.72 cm	44.45 cm	43.18 cm	43.18 cm	43.18 cm				

All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice.